

Single-Pole Preset Wide Slide Dimmer 600W



Features & Benefits

Maximum ratings are for continuous full load.

RFI suppression built in.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

For covering patents, see www.legrand.us/patents.

Many 1000W models fit standard Decorator plates.

Full-On bypass.

600W maximum rated dimmers can be ganged without de-rating.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007268829
Country Of Origin	Mexico	Application Sector	Residential
Standard	RoHS, CSA Listed, UL Listed		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60Hz Hz	Connection	Screw Terminals
Number of Poles	Single Pole	Wattage	600 W

Voltage

120 V

Load

Incandescent

Environmental Conditions

Humidity: Less than 95% non
condensing
