

## Rotary 1.5A 3-Speed De-Hummer Fan Speed Control



## Features & Benefits

Through the use of specially designed capacitive circuitry, these units can control fans at 3- or 4-speed levels in slide, rotary, and dual styles with virtually no fan motor noise.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007940015
Country Of Origin	Mexico	Features	3-Speed Fan Control, De-Hummer Fan Control
Switch Type	Rotary	Number of Switches	1
Application Sector	Multi-Dwelling Unit, Residential	Standard	CSA Listed, UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Fan Speed Control

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	48758
------------	-----	-----------------	-------

### Technical Information

Preset	No	Load Rating	120V 1.5A (FAN MOTOR)
--------	----	-------------	-----------------------

Dimming Compatibility	Fan Speed Only	Frequency Rating	60 Hz
Contact Rating	120V	Number of Poles	Single Pole
Wire Size	#14 - #10 AWG	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Flying Leads	Speed Range	3-Speed
Voltage	120 VAC	Load Type	AC Fan Motor
Environmental Conditions	Indoor Only		