

Rotary Fan Control 1.5A 4-Speed



Features & Benefits

Through the use of specially designed capacitive circuitry, these units can control fans at 3- or 4-speed levels in slide, rotary, and dual styles with virtually no fan motor noise.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007940114
Country Of Origin	Mexico	Features	4-Speed Fan Control, De-Hummer Fan Control
Switch Type	Rotary	Number of Switches	1
Application Sector	Multi-Dwelling Unit, Residential	Standard	CSA Listed, UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Fan Speed Control

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	48758
------------	-----	-----------------	-------

Technical Information

Preset	No	Load Rating	120V 1.5A (FAN MOTOR)
--------	----	-------------	-----------------------

Dimming Compatibility	Fan Speed Only	Frequency Rating	60 Hz
Contact Rating	120V	Number of Poles	Single Pole
Wire Size	#14 - #10 AWG	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Flying Leads	Speed Range	4-Speed
Voltage	120 VAC	Load Type	AC Fan Motor
Environmental Conditions	Indoor Only		