



Fan Speed Control Slide 5amp Preset Ivory

Features & Benefits

Full range speed control.

100 percent tested for symmetry for extended fan life.

Ferrite bar coil choke for excellent RFI suppression.

Utilizes standard Decorator wall plates.

Ground lead provided.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential
Standard	CSA Listed, UL Listed		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	48758
------------	-----	-----------------	-------

Technical Information

Connection	Pigtail Leads	Contact Rating	120
Amperage	5 A	Number of Poles	Single Pole
Speed Range	Variable	Voltage	120.0 V
Environmental Conditions	Indoor Only		