

Timer, 30min 1hp 20a 125v/10a 250-277volt, No Hold, Ivory



## Features & Benefits

Units with "Hold" feature may be turned counter-clockwise to hold the load on without timing function.

Quiet operation.

Available with or without hold.

Easily installed.

Accurate to +/- 5 percent.

Energy saving.

Turning clockwise causes unit to time load off after desired time delay.

Time range from 5 minutes to 12 hours.

Decorator styling.

Large head screw terminals.

Motor rated.

## Specifications

### General Info

Color	Ivory	UPC Number	785007970302
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential	Standard	CSA Listed, cULus, UL Listed

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	CSA Listed	Yes
CSA File Number	074656	cULus ListingNumber	103624

## Technical Information

---

Voltage	125 V, 250 V	Connection	Back & Side Wired
Coil Voltage	120VAC @ 60Hz	Timing Range	30 minutes
Action	Single Pole		

---