



100GBase-LR4 QSFP28 Compatible Transceiver, SMF, 1295nm-1309nm, 10km, LC Duplex, DDM, C-Temp



Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.
- Industry Leading Lifetime Warranty: For more information by product line, visit our [Warranty](#) page.
- 98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.
- Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875063780
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

Dimensions

Product Width US	18.35 mm	Product Depth US	125.35 mm
Product Height US	8.5 mm		

Technical Information

Fiber Optic Cable Type	Single-Mode	Max Distance Support	10 km
Operating Temperature Min	0 °C	Operating Temperature Max	70 °C
Connector Type	LC Duplex	Form Factor	QSFP28