



On-Q
Compression RG6U-Quad F Plug
Part No. AC300850



Optimize your installations with the Compression RG6U-Quad F Plug, available in a pack of 50. This water-resistant F compression connector is ideal for RG6/U Quad Shield Coax, widely used by satellite and cable TV service providers. It boasts a strong design that withstands a 55 lbs pull test and meets IPS-TP13 moisture resistance standards, ensuring reliable and long-lasting connections. The connector enables quick and efficient termination with a single squeeze of the handle. Available in a bulk pack of 50 for larger projects.

Features & Benefits

Seat and cut all wires at once with a squeeze of the handle

Pull Test: 55 lbs

Moisture Resistant: IPS-TP13

Available in 10 and 50 packs

Specifications

General Info

Product Line	On-Q	UPC Number	804428121824
Country Of Origin	Taiwan, Province Of China	Application Sector	Residential
Standard	RoHS		

Technical Information

Conductor Range	0.022 to 0.042 (diameter)	Connection	Shell and nut are nickel-plated brass
Temperature Rating	167° F	Amperage	10 A
Environmental Conditions	0		