




On-Q
Cat 5e Patch Cable, 25 ft, White
Part No. AC3525WHV1

This component rated Cat 5e patch cable is constructed with a low profile, snagless boot that protects the tab from catching on other cables in a high density patch panel application.



Features & Benefits

100 MHz patch cable supports 10 Gigabit Ethernet speeds	UL verified to support the Cat 5e performance patch cable specification
Snagless overmold prevents insertion tab from catching on other cables	24 AWG stranded patch cable :

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428031796	Country Of Origin	Taiwan, Province Of China
Application Sector	Residential	Standard	UL, CSA, FCC, 94V-0 Flame Retardant, RoHS

Dimensions

Product Length US	25.0 FT
-------------------	---------

Technical Information

Plug Type	RJ45	Attenuation	22
Wire Size	24 AWG	Number of Conductors	4
Conductor Material	Copper		