



Legrand
14 Foot Cat 6 Patch Cable, Blue
Part No. AC3614BEV1



This component rated Cat 6 patch cable is constructed with a low profile, snagless boot that protects the tab from catching on other cables in a high density patch panel application. These patch cables are 100% tested and certified.

Features & Benefits

250MHz patch cable fully supports 10 Gigabit Ethernet speeds.

UL verified to support the Cat 6 performance patch cable specification.

Snagless overmold prevents insertion tab from catching on other cables.

Patch cable exceeds 750 insertion cycles as specified in FCC part 68 Subpart.

Specifications

General Info

UPC Number 804428066842

Countries Of Origin China

Product Line On-Q

Application Sector Residential

Standard UL, CSA, FCC, TIA/EIA-568-B2-1 meets or exceeds Cat 6 standards, 94V-0 Flame Retardant, RoHS