



On-Q  
4K Premium High Speed HDMI™ Cable, 2m (10-pack)  
Part No. AC4K2MBK10

4K PREMIUM HIGH SPEED  
HDMI™ CABLE



Experience unparalleled video and audio quality with our 4K Premium Certified HDMI Cable. This 2-meter cable supports 4K resolution at 60Hz, ensuring crystal-clear visuals and immersive sound. Each cable is in-wall rated (CL3/FT4) for safe installation and supports high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD, and Dolby Atmos®. The gold-plated connectors resist corrosion and provide the highest level of signal conductivity. Each cable bears the Premium Certification label to guarantee authenticity. The 10-pack comes in a box with individually bagged cables inside.

## Features & Benefits

Supports 4K at 60Hz

CL3/FT4 Rated for in-wall use

Enhanced retention clips keep the cable firmly in place

Gold Plated Connector resists corrosion and provides the highest level of signal conductivity

Enhanced Audio Return Channel (eARC): Supports high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD and Dolby Atmos®

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

## Specifications

### General Info

Product Line	On-Q	Color	Black
Finish	Matte	UPC Number	804428435013
Country Of Origin	China		

### Dimensions

Product Width US	6.1 in	Product Weight US	2.97 lb
Product Height US	9.06 in	Product Length US	6.1 in

### Technical Information

Video Resolution	4K 60Hz	Jacket Application	In-Wall Rated
Cable Type	Premium HDMI	Jacket Rating	CL3 Rated, FT4 Rated

Data Transfer Rate	18 Gbps	Connector Type	HDMI
Video Input Support	HDMI	Conductor Material	Gold
Environmental Conditions	0.9		