




On-Q
4K Premium Certified HDMI Cable, 3m (10-pack)
Part No. AC4K3MBK10

4K PREMIUM CERTIFIED HDMI CABLE



The premium certified 4K (18Gbps) HDMI cable supports 4K at 60Hz. Each length is in-wall rated (CL3/FT4) and supports a high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD and Dolby Atmos®. Each cable bears the Premium Certification label to guarantee authenticity.

10-pack: Box with individually bagged cables inside

Features & Benefits

Supports 4K at 60Hz

CL3/FT4 Rated for in-wall use

Enhanced retention clips keep the cable firmly in place

Gold Plated Connector resists corrosion and provides the highest level of signal conductivity

Enhanced Audio Return Channel (eARC): Supports high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD and Dolby Atmos®

Specifications

General Info

Product Line	On-Q	Color	Black
Finish	Matte	Country Of Origin	China

Dimensions

Product Width US	6.1 in	Product Weight US	4.83 lb
Product Height US	14.17 in	Product Length US	6.1 in

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Video Resolution	4K 60Hz
Jacket Application	In-Wall Rated	Cable Type	Premium HDMI

Jacket Rating	CL3 Rated, FT4 Rated	Data Transfer Rate	18 Gbps
Connector Type	HDMI	Conductor Material	Gold
Environmental Conditions	0.9		
