




adorne Collection
adorne® 0-10V Paddle™ Dimmer
Part No. ADPD4FBL3P2W4



Perfect for anywhere you'd like the combined power of on/off and dimmable lighting control options. Turn lights on or off with a simple rocking motion, or slide to dim to your preferred light level. Use this device on its own to control a light or fixture from a single location, or pair with a 3-way switch to control a single light source from two locations. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

For use with 0-10V bulbs, and features smooth paddle action for turning lights on and off, plus easily adjusts lights to your preferred light level.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Color	White	UPC Number	785007052688
Country Of Origin	China	Product Line	Pass & Seymour
Number of Switches	1	Type	Dimmer
Warranty Type	Limited Lifetime Warranty	Standard	cULus,

Technical Information

Wattage	700 W	Number of Poles	Single Pole, 3-Way
Number of Gangs	1	Voltage	0 V, 10 V
Mounting Type	Box	Connection	Screw Terminals
Load	Fluorescent/LED	Connection Type	Internal Pressure Plates