




adorne Collection
adorne® Incandescent/Halogen Touch™ Wi-Fi Ready Master Dimmer, Magnesium
Part No. ADTH600RMHM1



Combine Wi-Fi Lighting Control with sleek touch technology and the option to dim, for truly contemporary control. The Touch Wi-Fi Ready Master Dimmer is a programmable light switch and dimmer combination that pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System in your home. (For 3-way, or multi-way applications, use one master device with additional remote devices.) Turn lights on/off, or adjust their brightness, with just the touch of a finger. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light. For use with incandescent/halogen bulbs.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Pair with a Touch Wi-Fi Ready Remote Dimmer to allow for 3-way control. Simply follow the provided instructions after installing to pair with the Master Dimmer.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
UPC Number	804428065609	Country Of Origin	United States
Number of Switches	1	Application Sector	Residential
Standard	cULus, FCC, UL 1472	Warranty Type	2-Year Limited Warranty

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Conformant Yes

Technical Information

Actuator Touch Frequency Rating 900 M (RF) Hz

Number of Gangs 1 Number of Poles Single Pole, 3-Way, Multi-Location

Wattage 600 W Mounting Type Box

Voltage 120 V Connection Type Internal Pressure Plates

Load Incandescent, Halogen Environmental Conditions 0 to 80 (relative humidity, non-condensing)
