



adorne Collection  
**Discontinued - adorne Touch Wi-Fi Ready Remote Dimmer**  
Part No. ADTHRRG1



Combine Wi-Fi Lighting Control with sleek touch technology and the option to dim, for truly contemporary control. The Touch Wi-Fi Ready Remote Dimmer works in conjunction with an adorne Hub and a Wi-Fi Ready Master Dimmer for 3-way control. Use the dimmer to turn lights on/off, or adjust brightness, all with just the touch of a finger. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes. Installs in 25 minutes or less.

Allows 3-way application when paired with a Wi-Fi Ready Master Dimmer, letting you control a light or fixture from an additional location without running new wires. Pair with the Wi-Fi Ready Master Dimmer via the easy-to-follow instructions. Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems. Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Graphite
Country Of Origin	China	Features	Indicator Lights, Smart Lighting
Switch Type	Touch	Number of Switches	1
Works With	Amazon Alexa, Control4, Elan, Google Assistant, Radio Frequency, RTI, URC	Warranty Type	1-Year Limited Warranty

### Technical Information

Number of Gangs	1	Amperage	5.5 A
-----------------	---	----------	-------

Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon	Number of Poles	3-Way, Multi-Location, Single Pole
Mounting Type	Box	Voltage	120.0 V
Connection Type	Internal Pressure Plates		