



Turn lights on/off, or dim, with just a soft tap of a finger, thanks to inventive micro-movement technology. Meant for single fixtures and small lighting groups that do not exceed 700W. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.	Activation with a softTap of a finger
Micro-movement operation for dimming	Compatible with incandescent, halogen, CFL, Fluorescent, or LED light bulbs

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Metallic	UPC Number	785007030464
Country Of Origin	China	Features	Auto-Calibration (Trim), High-End Trim (Dim Range), Locator Light, Low-End Trim (Dim Range)
Switch Type	Digital, Multi-Location, Single Pole 3-Way, sofTap	Number of Switches	1
Device Front Face Size	Full-Size	Device Backbody Size	Plus-Size
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

Technical Information

Preset	Yes	Load Rating	120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 700W (ELV), 120V 8A (EFL)
--------	-----	-------------	--

Dimming Compatibility	Forward or Reverse Selectable Phase	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	CFL, Fluorescent, Halogen, Incandescent, LED
Number of Poles	Multi-Location, Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120 VAC		