



adorne Collection
adorne® sofTap™ Wi-Fi Ready Remote Dimmer, Magnesium
Part No. ADTPRRM1



Working in conjunction with an adorne Hub and a sofTap Wi-Fi Ready Master Dimmer for 3-way control. Use the dimmer to turn lights on/off, or adjust brightness, all with just the lightest tap of a finger. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less.

Allows 3-way application when paired with a Wi-Fi Ready Master Dimmer, letting you control a light or fixture from an additional location without running new wires. Pair with the Wi-Fi Ready Master Dimmer via the easy-to-follow instructions.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Specifications

General Info

| | | | |
|-------------------|---|--------------------|----------------------------------|
| Product Line | Pass & Seymour | Color | Magnesium |
| Country Of Origin | United States | Features | Indicator Lights, Smart Lighting |
| Switch Type | sofTap | Number of Switches | 1 |
| Works With | Amazon Alexa, Control4, Elan, Google Assistant, Radio Frequency, RTI, URC | Application Sector | Residential |
| Standard | cULus, FCC, UL 1472 | Warranty Type | 1-Year Limited Warranty |

Listing Agencies / 3rd Party Agencies

| | | | |
|--------------|-----|---------------|-----|
| cULus Listed | Yes | FCC Compliant | Yes |
|--------------|-----|---------------|-----|

Additional Information

RoHS Conformant Yes

Technical Information

| | | | |
|------------------|------------------------------------|--------------------------|---|
| Frequency Rating | 900 M (RF) Hz | Number of Gangs | 1 |
| Amperage | 5.5 A | Bulb Compatibility | CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon |
| Number of Poles | 3-Way, Multi-Location, Single Pole | Mounting Type | Box |
| Voltage | 120 V | Connection Type | Internal Pressure Plates |
| Load | Auxiliary Remote Dimmer - No Load | Environmental Conditions | 0 to 80% (relative humidity, non-condensing) |