



adorne Collection  
adorne® sofTap™ Wi-Fi Ready Remote Dimmer  
Part No. ADTPRRW1



Working in conjunction with an adorne Hub and a sofTap Wi-Fi Ready Master Dimmer for 3-way control. Use the dimmer to turn lights on/off, or adjust brightness, all with just the lightest tap of a finger. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

Installs in 25 minutes or less.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Allows 3-way application when paired with a Wi-Fi Ready Master Dimmer, letting you control a light or fixture from an additional location without running new wires. Pair with the Wi-Fi Ready Master Dimmer via the easy-to-follow instructions.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Color	White	UPC Number	804428065739
Country Of Origin	United States	Product Line	Pass & Seymour
Number of Switches	1	Application Sector	Residential
Warranty Type	1-Year Limited Warranty	Standard	cULus, FCC, UL 1472

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Additional Information

---

RoHS Conformant    Yes

---

## Technical Information

---

Number of Poles	Single Pole, 3-Way, Multi-Location	Number of Gangs	1
Voltage	120 V	Mounting Type	Box
Frequency Rating	900 M (RF) Hz	Load	Auxiliary Remote Dimmer - No Load
Connection Type	Internal Pressure Plates	Environmental Conditions	0 to 80 (relative humidity, non- condensing)

---