



adorne Collection
adorne® Whisper™ Wi-Fi Ready Master Dimmer No Neutral
Part No. ADWR600RMHW1



This dimmer combines the flexibility of Wi-Fi-Lighting Control, with a unique manual control experience that uses a whisper-soft motion to dim and brighten lights. Pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Turn lights on/off or dim with a whisper-soft motion; or create custom lighting scenes lights through the Legrand Lighting Control app for your smartphone or tablet. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Pair with a Whisper Wi-Fi Ready Remote Dimmer for 3-way control.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	804428431343	Country Of Origin	China
Number of Switches	1	Application Sector	Residential
Standard	UL, FCC, cULus, RoHS		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Conformant Yes

Technical Information

Frequency Rating	900 Hz	Number of Gangs	1
Number of Poles	Single Pole, 4-Way, Multi-Location	Wattage	600 W
Mounting Type	Box	Voltage	120 V
Connection Type	Internal Pressure Plates		
