



This dimmer combines the flexibility of Wi-Fi-Lighting Control, with a unique manual control experience that uses a whisper-soft motion to dim and brighten lights. Pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Turn lights on/off or dim with a whisper-soft motion; or create custom lighting scenes lights through the Legrand Lighting Control app for your smartphone or tablet. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with Amazon Alexa and Google Home. A Tru-Universal Dimmer, this device works with virtually any 120V dimmable bulb or fixture. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.

Works with virtually any 120V dimmable bulb or fixture.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Pair with a Whisper Wi-Fi Ready Remote Dimmer for 3-way control.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	804428122142	Country Of Origin	China
Number of Switches	1	Application Sector	Residential
Standard	UL, FCC, cULus, RoHS		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Frequency Rating	900 M (Top Dog Radio Protocol) Hz	Connection	Screw Terminals
------------------	-----------------------------------	------------	-----------------

Number of Gangs	1	Number of Poles	Single Pole, 4-Way
-----------------	---	-----------------	--------------------

Wattage	700 W	Mounting Type	Box
---------	-------	---------------	-----

Voltage	120 V	Connection Type	Internal Pressure Plates
---------	-------	-----------------	--------------------------

Load	Dimmable Incandescent, Halogen, Magnetic Low voltage (ML), Electronic Low voltage (EL) in Forward or Reverse Phase, CFL/LED	Environmental Conditions	0 to 80 (relative humidity, non-condensing)
------	---	--------------------------	---
