



Add contemporary style, safely, to kitchens, bathrooms and more, with GFCI Outlets from the adorene Collection. Meeting Electrical Code\* for ground fault protection in the home, GFCI outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. The adorene GFCI Outlets also self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. \*GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the adorene® Collection, sold separately.

### Features & Benefits

- For complete installation, device must be paired with an adorene® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.
- Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Configuration easily supports two plugs and offers the capacity of a standard 15A outlet, in a uniquely contemporary design.
- Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Replaces any standard outlet with ease, in as little as 10 minutes.
- More color options available to fit any style, including finishes to match current hardware and lighting trends.

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Graphite
Country Of Origin	China	Number of Receptacles	2
Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

#### Dimensions

Product Width US	1.82 in	Product Depth US	1.76 in
------------------	---------	------------------	---------

Product Height US	3.0 in
-------------------	--------

Technical Information

Is Tamper-Resistant	Yes	Connection	Side & Back Wire
Number of Gangs	1	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Voltage	125.0 V	Connection Type	Internal Pressure Plates
Environmental Conditions	95% (relative humidity, non-condensing)		