



Ortronics

Discontinued - Arista AOC-40G-Q-S-10M Compatible Active Optical Cable

Part No. AOC-40G-Q-S-10M-L

10m Arista AOC-40G-Q-S-10M Compatible 40GBase-AOC QSFP+ to 4 x SFP+ Breakout (MMF, 850nm, LSZH) Active Optical Cable



Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875087618
Country Of Origin	China	Warranty Type	Lifetime
Type	Active Optical Cable		

Technical Information

Max Distance Support	10 m	Data Transfer Rate	40 Gbps
Wavelength	850 nm		