



**adorne Collection**  
adorne® 15A Tamper-Resistant Dual-Controlled Outlet  
Part No. ARCD152M10



A modern upgrade for style, safety and energy management, this tamper-resistant, dual-controlled outlet from the adorne Collection installs easily in place of an existing outlet. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

### Features & Benefits

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Independently cut power to either plug when not in use to conserve energy.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

### Specifications

#### General Info

Color	Magnesium	UPC Number	785007050707
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential	Number of Receptacles	2
Warranty Type	Limited Lifetime Warranty	Standard	CULUS

#### Dimensions

Product Width US	1.77 in	Product Length US	2.12 in
Product Depth US	1.73 in		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Number of Poles	Double Pole	Number of Gangs	1
Voltage	125 VAC	Mounting Type	Box

---

Connection	Side and Back Wire	Phase	Single
Wire Size	#14 - #10 AWG	Number of Wires	3
Connection Type	Internal Pressure Plates		

---