




adorne Collection
adorne® 15A Energy-Saving On/Off Outlet, Magnesium
Part No. ARPS152M4



Add stunning, modern style with this outlet from the adorne Collection, while conserving energy when it's not in use. It allows you to stop the flow of power whenever you don't need it, for easy energy management. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

GETTING STARTED: For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Cut power to the outlet when not in use to conserve energy.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007022728
Country Of Origin	China	Number of Receptacles	2
Device Front Face Size	Full-Size	Device Backbody Size	Full-Size
Outlet Type	Energy Saving On/Off, Tamper-Resistant	Application Sector	Residential
Standard	CULUS	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

Dimensions

Product Width US	2.66 in	Product Depth US	1.73 in
Product Height US	1.77 in		

Technical Information

Phase	Single	Connection	Side and Back Wire
Number of Wires	3	Number of Gangs	1
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Box
Connection Type	Internal Pressure Plates	Environmental Conditions	95% (relative humidity, non-condensing)