



adorne Collection
adorne® Pop-Out Outlet with Gloss White Wall Plate, White
Part No. ARPTR151GW2WP



The cleverest way to add power and style, the Pop-Out Outlet extends to offer 3-plug access, then uniquely disappears back into the wall with a simple push when not in use. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Perfect anywhere you'd like to hide outlets when not in use, for added style and safety.

Provides additional power with 3-plug access when extended from wall.

Disappears back into the wall with a simple push when not needed.

Installs easily in as little as 15 minutes.

Comes with a special frame for mounting and requires a deep electrical outlet (22.5 cubic inches). No new wires required for typical installation.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|-----------------------|---------------------------|--------------------|----------------------------------|
| Product Line | Pass & Seymour | Color | Gloss White |
| UPC Number | 785007158458 | Country Of Origin | China |
| Number of Receptacles | 3 | Features | Pop-Out |
| Outlet Type | Pop-Out, Tamper-Resistant | Application Sector | Multi-Dwelling Unit, Residential |
| Wall Plate Included | Yes | Warranty Type | Limited Lifetime Warranty |

Dimensions

| | | | |
|------------------|---------|------------------|--------|
| Product Width US | 3.45 in | Product Depth US | 2.6 in |
|------------------|---------|------------------|--------|

| | |
|-------------------|---------|
| Product Height US | 5.13 in |
|-------------------|---------|

Technical Information

| | | | |
|---------------------|-------------|----------------------|--------------------------|
| Is Tamper-Resistant | Yes | Connection Location | Back Only |
| Number of Wires | 3 | Number of Gangs | 1 |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 14 - 12 AWG | Indoor/Outdoor | Indoor |
| Mounting Type | Box | Wire Connection Type | Internal Pressure Plates |
| Voltage | 125.0 V | | |