



adorne Collection
adorne® 20A 1-Gang Pop-Out Outlet, Magnesium
Part No. ARPTR201GM2



The cleverest way to add power and style, the Pop-Out Outlet extends to offer 2-plug access, then uniquely disappears back into the wall with a simple push when not in use. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Provides 2-plug access when extended from wall.

Installs easily in as little as 15 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Perfect anywhere you'd like to hide outlets when not in use, for added style and safety.

Disappears back into the wall with a simple push when not needed.

Comes with a special frame for mounting and requires a deep electrical outlet (22.5 cubic inches). No new wires required for typical installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007060522
Country Of Origin	China	Number of Receptacles	2
Features	Pop-Out	Outlet Type	Pop-Out, Tamper-Resistant
Application Sector	Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	2.99 in	Product Depth US	2.6 in
Product Height US	4.88 in		

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back Only
Number of Wires	3	Number of Gangs	1
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
Mounting Type	Box	Wire Connection Type	Internal Pressure Plates
Voltage	125.0 V	Environmental Conditions	95% (relative humidity, non-condensing)