



A modern upgrade for style and safety, this 15A tamper-resistant designer outlet from the adorne Collection installs easily for the basic power every home needs, while elevating your space. The adorne wall outlets are made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

- Replaces any standard outlet with ease, in as little as 10 minutes
- Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect
- More color options available to fit any style, including finishes to match current hardware and lighting trends
- Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007022872
Country Of Origin	China	Number of Receptacles	2
Application Sector	Residential	Standard	CULUS

Additional Information

Prop 65 Warning Required	No
--------------------------	----

Technical Information

Phase	Single	Connection	Side and Back Wire
-------	--------	------------	--------------------

Number of Wires	3	Number of Gangs	1
Number of Poles	Double Pole	Wire Size	#14 - #10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Mounting Type	Box	Voltage	125 VAC
Connection Type	Internal Pressure Plates	Environmental Conditions	95 (relative humidity, non-condensing)
