



adorne Collection
adorne® Dual-USB Outlet , Magnesium
Part No. ARTRUSB153M4



Get a full battery for your phones, tablets and more with the convenience of built-in charging. Including two USB Type-A connections and replacing a traditional outlet in as little as ten minutes, this adorne USB Outlet provides easy-to-access charging without sacrificing a plug or finding that bulky adapter. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Features a total charging capacity of 3.1A.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisible shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Replaces a traditional outlet easily, in as little as 10 minutes.

Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging
Outlet Type	Indoor, Residential, Tamper-Resistant, USB-Charging	Standard	UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Outlet

Dimensions

Product Width US	1.77 in	Product Depth US	1.48 in
Product Height US	2.65 in		

Technical Information

USB Amperage	3.1 A	Phase	Single
Connection	Side and Back Wire	Number of USBs	2
Number of Wires	3	Number of Gangs	1
USB Power Output	15 W	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Mounting Type	Box	Voltage	125.0 V
Connection Type	Internal Pressure Plates	Environmental Conditions	95% (relative humidity, non-condensing)