



radiant Collection
radiant® 15A Tamper-Resistant USB Type C/C Outlet
Part No. ASI01-R26USBCCNICC6

Get a full battery for your phones, tablets and more with the convenience of built-in charging. This tamper-resistant USB outlet features two USB Type-C connections to accommodate the latest mobile devices – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, this outlet offers accessible charging without sacrificing your plugs, and features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Accommodates the latest mobile devices with two built-in connections for the newer USB Type-C, which features a smaller, reversible connector and high-speed specs.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
UPC Number	785007181005	Country Of Origin	China
Features	USB-C Charging	Outlet Type	Indoor, Residential, Tamper-Resistant, USB-Charging

Dimensions

Product Width US	1.69 in	Product Depth US	1.35 in
Product Height US	4.18 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
---------------------	-----	----------	------

Mounting Type	Box	Voltage	125.0 V
---------------	-----	---------	---------
