



A modern twist on classic up-and-down switch control, the Paddle Switch lets you turn lights on and off with ease. Use this device on its own to control a light or fixture from a single location, or pair with a second switch or dimmer to control a single light source from two locations. Made exclusively for use with screwless Wall Plates from the adore® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adore® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.	Laser engraved at the factory with the word "Garbage Disposal"
Perfect for anywhere you'd like to upgrade the look of a standard switch	Control device from one location (single-pole operation)
Pair with matching Paddle Dimmer or Paddle Fan Speed Control to create a uniform look throughout a room	

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007198256
Country Of Origin	China	Features	Engraved
Device Front Face Size	Full-Size	Device Backbody Size	Full-Size
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.77 in	Product Depth US	1.5 in
Product Height US	1.77 in		

Technical Information

Connection	Screw Terminals	Amperage	15 A
Wire Size	#14 - #10 AWG	Connection Type	Internal Pressure Plates