




adorne Collection  
adorne® sofTap™ Wi-Fi Ready Master Switch  
Part No. ASTP155RMM1



The sofTap Wi-Fi Ready Master Switch pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Manually turn lights on/off with the soft tap of a finger, or enjoy mobile control and create custom lighting scenes to control lights through the Legrand Lighting Control app for smartphones or tablets. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

- Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light. **Pair with a sofTap Wi-Fi Ready Remote Switch for 3-way control.**
- Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app. **Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.**
- Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate. **More color options available to fit any style, including finishes to match current hardware and lighting trends.**
- Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

## Specifications

### General Info

Color	Magnesium	UPC Number	804428065852
Country Of Origin	United States	Product Line	Pass & Seymour
Number of Switches	1	Application Sector	Residential
Warranty Type	1-Year Limited Warranty	Standard	UL 508, FCC cULus, RoHS

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Additional Information

---

RoHS Conformant      Yes

---

## Technical Information

---

Wattage	1800 W	Number of Poles	Single Pole, 3-Way, Multi-Location
Number of Gangs	1	Voltage	120 V
Mounting Type	Box	Supply Voltage	120 V
Connection Type	Internal Pressure Plates	Environmental Conditions	0 to 80 (relative humidity, non-condensing)

---