



adorne Collection
adorne® Whisper® Switch, Graphite, with Microban®
Part No. ASWR1532G4



Control your lights with a soft, fluid motion using this modern light switch.

This switch* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Controls light with a gentler action in an elegant design. Usable in both single-pole and 3-way applications.

Specifications

General Info

| | | | |
|-------------------|---------------------------|--------------------|--------------------------|
| Product Line | Pass & Seymour | Color | Graphite |
| Country Of Origin | China | Features | Antimicrobial Protection |
| Switch Type | Whisper | Number of Switches | 1 |
| Warranty Type | Limited Lifetime Warranty | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.77 in | Product Depth US | 1.63 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|---------|
| Product Height US | 1.77 in |
|-------------------|---------|

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Gangs | 1 | Amperage | 15 A |
|-----------------|---|----------|------|

| | | | |
|-----------------|--------------------|---------------|-----|
| Number of Poles | 3-Way, Single Pole | Mounting Type | Box |
|-----------------|--------------------|---------------|-----|

| | | | |
|---------|---------|-----------------|--------------------------|
| Voltage | 120.0 V | Connection Type | Internal Pressure Plates |
|---------|---------|-----------------|--------------------------|