



Pass and Seymour  
Strain Relief Grips  
Part No. BOX140

Wide range, Straight male, Dust tight grip. 2-inch NPT, 1.400-1.750-inch.



## Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and Includes insulated power centers. bushing.

1400 lbs breaking strength rating (in US lbs)

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007996210
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Cord Grip		

### Dimensions

Product Width US	1.75 in	Product Length US	2.0 in
Cable Diameter Range	1.40-1.75 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Maximum Cable Range	1.4 in	Minimum Cable Range	1.75 in
Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
Mounting	Consult the Factory for Mounting Recommendations	Load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord