



Pass and Seymour
Strain Relief Grips
Part No. BOX30

Wide Range, Straight Male, Dust Tight Grip, 1/2-inch, 0.300-0.430.



Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and Includes insulated power centers. bushing.

300 lbs breaking strength rating (in US lbs)

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007996159
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Cord Grip		

Dimensions

Product Width US	0.43 in	Product Length US	0.5 in
Cable Diameter Range	0.300-0.430 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Maximum Cable Range	0.3 in	Minimum Cable Range	0.43 in
Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
Mounting	Consult the Factory for Mounting Recommendations	Load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord