



**Pass and Seymour**  
Strain Relief Grips  
Part No. BOX70

Wide range, Straight male, Dust tight grips. 1" NPT, 0.700-0.970"



### Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and power centers.

Includes insulated bushing.

700 lbs breaking strength rating (in US lbs)

### Specifications

#### General Info

UPC Number	785007996180	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Type	Dust Tight	Construction	Various Types of Pulling, Support and Strain Relief Grips
Standard	UL/CSA Approval (consult factory)		

#### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

#### Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	NPT Size: 1; Cable Dia. Range: 0.700-1.000
Capacity	Various Cable Diameter Ranges	Load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.