



Pass and Seymour
Titan Series Incandescent Dimmer, Black
Part No. CD1600BK

Slide Dimmer, Single Pole 1600W 120V, Red



Features & Benefits

Field configurable wall plate system.

Adjustable top end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

For covering patents, see www.legrand.us/patents.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of de-rating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Specifications

General Info

Color	Black	UPC Number	785007302479
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Commercial	Type	Dimmer
Standard	cULus, California Title 24 Compliant		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	95219
--------------	-----	---------------------	-------

Technical Information

Wattage	1600 W	Number of Poles	Single Pole
---------	--------	-----------------	-------------

Voltage	120 V	Frequency Rating	60 Hz
---------	-------	------------------	-------

Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95
------	--	--------------------------	--

Operating Cycles	100
------------------	-----
