



Pass and Seymour  
Discontinued - Titan™ Series Fluorescent 3-Wire Dimmer, Red  
Part No. CD3FB10277RED



Ganging conventional dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change all that. Unlike the others, Titan Dimmers are a complete solution that saves time and money and offers end-users a superior, more convenient, better-looking multi-gang installation.

## Features & Benefits

For use with 3 wire 120V and 277V fluorescent dimming ballasts.

Labeling system

Shipped with protective film

Superior ratings with a minimum of derating when ganged

Available in single pole slide-to-OFF and single pole/3-way preset models

Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system

Field configurable wall plate system

Adjustable low end output voltage

Rugged construction

Simple to plan the rough-in

Attractive European styling. Eye-catching packaging

Blank center plate included

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
------------------	-----	------------------	-------

---

Amperage	10 A	Number of Poles	Single Pole
Voltage	277.0 V	Load	Up to rating of device (including de-rating)
Environmental Conditions	Non-Condensing Humidity: Less than 95%		

---