



Pass and Seymour
Titan Series Fluorescent 3 Wire Dimmer, Light Almond
Part No. CD3FB103P277LA

Slide Dimmer, Electronic Single-Pole/3-Way 3-Wire PRSET 10A277V



Features & Benefits

For use with 3 wire 120V and 277V fluorescent dimming ballasts.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of derating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Exclusive adaptor kit to install other Decorator opening devices under the Titan:
wall plate system.

For covering patents, see www.legrand.us/patents.

Field configurable wall plate system.

Adjustable low end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling. Eye-catching packaging.

Blank center plate included.

Specifications

General Info

| | | | |
|-------------------|---|--------------------|--------------|
| Product Line | Pass & Seymour | UPC Number | 785007255614 |
| Country Of Origin | China | Application Sector | Commercial |
| Standard | cULus, California Title 24 Compliant | Type | Dimmer |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|--------------------------|---------------------------------------|------------------|--|
| Operating Cycles | 100 | Frequency Rating | 60 Hz |
| Voltage | 277 V | Load | Up to rating of device (including de-rating) |
| Environmental Conditions | Non-Condensing Humidity: Less than 95 | | |
