



Pass and Seymour
Titan Series Fluorescent 3 Wire Dimmer, Black
Part No. CD3FB163PBK

Slide Dimmer, Electronic Single-Pole/3-Way 3-Wire PRESET
16A120V



Features & Benefits

For use with 3 wire 120V and 277V fluorescent dimming ballasts

Labeling system

Shipped with protective film

Superior ratings with a minimum of derating when ganged

Available in single pole slide-to-OFF and single pole/3-way preset models

Exclusive adaptor kit to install other Decorator opening devices under the Titan:
wall plate system

For covering patents, see www.legrand.us/patents

Field configurable wall plate system

Adjustable low end output voltage

Rugged construction

Simple to plan the rough-in

Attractive European styling. Eye-catching
packaging

Blank center plate included

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007255577	Country Of Origin	China
Application Sector	Commercial	Standard	cULus, California Title 24 Compliant
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
------------------	-----	------------------	-------

Voltage	120 V	Load	Up to rating of device (including de-rating)
---------	-------	------	--

Environmental Conditions	Non-Condensing Humidity: Less than 95		
--------------------------	---------------------------------------	--	--
