



Pass and Seymour  
**Discontinued - Titan Series Fluorescent 3-Way Preset 4 Wire Dimmer, Ivory**  
Part No. CD4FB3PI



Ganging conventional dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change all that. Unlike the others, Titan Dimmers are a complete solution that saves time and money and offers end-users a superior, more convenient, better-looking multi-gang installation.

## Features & Benefits

Field configurable wall plate system	Labeling system
Adjustable low end output voltage	Shipped with protective film
Rugged construction	Superior ratings with a minimum of derating when ganged
Simple to plan the rough-in	Available in single pole slide-to-OFF and single pole/3-way preset models
Attractive European styling. Eye-catching packaging	Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system
Blank center plate included	Requires BZ50 24 VDC Power Pack

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

### Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	10 A	Voltage	24.0 V
Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95%