



Pass and Seymour  
Discontinued - Titan Series LED 4-Wire Single-Pole/3-Way Preset Dimmer, Ivory  
Part No. CD4FBL3PI



## Features & Benefits

Includes integrated power pack and blank center plate.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of derating when ganged.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Field configurable wall plate system.

Adjustable low end trim.

Rugged construction.

Simple to plan the rough-in.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Application Sector	Commercial
Standard	RoHS, cULus	Type	Dimmer

### Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Amperage	10 A	Voltage	120.0 V
Load	Fluorescent	Environmental Conditions	Humidity: Less than 95% non condensing