



Pass and Seymour
Titan Series Incandescent Dimmer, White
Part No. CD700W

Slide Dimmer, Single-Pole 700W 120V



Features & Benefits

Field configurable wall plate system.

Adjustable top end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

For covering patents, see www.legrand.us/patents.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of de-rating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007301700	Country Of Origin	China
Application Sector	Commercial	Standard	cULus, California Title 24 Compliant
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
------------------	-----	------------------	-------

Number of Poles	Single Pole	Wattage	700 W
-----------------	-------------	---------	-------

Voltage	120 V	Load	Up to rating of device (including de-rating)
---------	-------	------	--

Environmental Conditions	Non-Condensing Humidity: Less than 95		
--------------------------	---------------------------------------	--	--
