

Slide Dimmer, Electronic Single-Pole2Wire 10A



Features & Benefits

For use with 2 wire 120V and 277V fluorescent dimming ballasts.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of derating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Field configurable wall plate system.

Adjustable low end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------------------------------------|
| Product Line | Pass & Seymour | Color | Brown |
| UPC Number | 785007302660 | Country Of Origin | China |
| Application Sector | Commercial | Standard | cULus, California Title 24 Compliant |
| Type | Dimmer | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------|-----|------------------|-------|
| Operating Cycles | 100 | Frequency Rating | 60 Hz |
|------------------|-----|------------------|-------|

| | | | |
|-----------------|-------------|---------|-------|
| Number of Poles | Single Pole | Voltage | 120 V |
|-----------------|-------------|---------|-------|

| | | | |
|------|--|--------------------------|--|
| Load | Up to rating of device (including de-rating) | Environmental Conditions | Non-Condensing Humidity: Less than 95 |
|------|--|--------------------------|--|
