



Pass and Seymour
Titan Series Fluorescent 2 Wire Dimmer, White
Part No. CDFB103P277W

Slide Dimmer, Electronic Single Pole/3Way 2Wire 10A 277V, Ivory



Features & Benefits

- | | |
|--|---|
| For use with 2 wire 120V and 277V fluorescent dimming ballasts. | Field configurable wall plate system. |
| Labeling system. | Adjustable low end output voltage. |
| Shipped with protective film. | Rugged construction. |
| Superior ratings with a minimum of derating when ganged. | Simple to plan the rough-in. |
| Available in single pole slide-to-OFF and single pole/3-way preset models. | Attractive European styling. |
| Eye-catching packaging. | Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. [See Page N-29.] |
| Blank center plate included. | For covering patents, see www.legrand.us/patents . |

Specifications

General Info

Color	White	UPC Number	785007303353
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Commercial	Type	Dimmer
Standard	cULus, California Title 24 Compliant		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Voltage	277 V	Frequency Rating	60 Hz
Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95
Operating Cycles	100		