



Pass and Seymour
Discontinued - Titan Series Fluorescent 2 Wire Dimmer, Red
Part No. CDFB103PRED



Slide Dimmer, Electronic Single Pole/3Way 2Wire PRESET 10A, Red

Features & Benefits

For use with 2 wire 120V and 277V fluorescent dimming ballasts.

Field configurable wall plate system.

Labeling system.

Adjustable low end output voltage.

Shipped with protective film.

Rugged construction.

Superior ratings with a minimum of derating when ganged.

Simple to plan the rough-in.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Attractive European styling.

Eye-catching packaging.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

Blank center plate included.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|--------------------------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Red |
| Country Of Origin | China | Application Sector | Commercial |
| Standard | cULus, California Title 24 Compliant | Type | Dimmer |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------|--|--------------------------|---|
| Operating Cycles | 100 | Frequency Rating | 60 Hz |
| Amperage | 10 A | Voltage | 120.0 V |
| Load | Up to rating of device (including de-rating) | Environmental Conditions | Non-Condensing Humidity: Less than 95% |
