



Pass and Seymour
Discontinued - Titan Series Fluorescent 2 Wire Dimmer, White
Part No. CDFB163PW



Ganging conventional dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change all that. Unlike the others, Titan Dimmers are a complete solution that saves time and money and offers end-users a superior, more convenient, better-looking multi-gang installation.

Features & Benefits

| | |
|--|---|
| For use with 2 wire 120V and 277V fluorescent dimming ballasts | Field configurable wall plate system |
| Labeling system | Adjustable low end output voltage |
| Shipped with protective film | Rugged construction |
| Superior ratings with a minimum of derating when ganged | Simple to plan the rough-in |
| Available in single pole slide-to-OFF and single pole/3-way preset models | Attractive European styling. Eye-catching packaging |
| Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system | Blank center plate included |

Specifications

General Info

| | | | |
|-------------------|--------------------------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | China | Application Sector | Commercial |
| Standard | cULus, California Title 24 Compliant | Type | Dimmer |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------|--|--------------------------|---|
| Operating Cycles | 100 | Frequency Rating | 60 Hz |
| Amperage | 16 A | Voltage | 120.0 V |
| Load | Up to rating of device (including de-rating) | Environmental Conditions | Non-Condensing Humidity: Less than 95% |