



Pass and Seymour
Discontinued - Titan Series Fluorescent 2 Wire Dimmer, Ivory
Part No. CDFB16I



Features & Benefits

For use with 2 wire 120V and 277V fluorescent dimming ballasts.

Field configurable wall plate system.

Labeling system.

Adjustable low end output voltage.

Shipped with protective film.

Rugged construction.

Superior ratings with a minimum of derating when ganged.

Simple to plan the rough-in.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Attractive European styling.

Eye-catching packaging.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

Blank center plate included.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------------------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| UPC Number | 785007302745 | Country Of Origin | China |
| Application Sector | Commercial | Standard | cULus, California Title 24 Compliant |
| Type | Dimmer | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|-----------------------|-------------|--------------------------|---|
| cULus Listed | Yes | | |
| Technical Information | | | |
| Operating Cycles | 100 | Amperage | 16 A |
| Number of Poles | Single Pole | Environmental Conditions | Non-Condensing Humidity: Less than 95% |