



Pass and Seymour  
Titan Series Fluorescent 2 Wire Dimmer, Ivory  
Part No. CDFB73P277I

Slide Dimmer, Electronic Single-Pole/3-Way 2Wire 7A 277V



## Features & Benefits

For use with 2 wire 120V and 277V fluorescent dimming ballasts.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of derating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Field configurable wall plate system.

Adjustable low end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007303285	Country Of Origin	China
Application Sector	Commercial	Standard	cULus, California Title 24 Compliant
Type	Dimmer		

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Operating Cycles	100	Frequency Rating	60 Hz
------------------	-----	------------------	-------

---

Voltage	277 V	Load	Up to rating of device (including de-rating)
---------	-------	------	--

---

Environmental Conditions	Non-Condensing Humidity: Less than 95
--------------------------	---------------------------------------

---