



Pass and Seymour
Titan Series Magnetic Low-Voltage Dimmer, Brown
Part No. CDLV1100

Slide Dimmer, Low Voltage, Single Pole 1100VA, Light Almond



Features & Benefits

Field configurable wall plate system.

Adjustable low end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system.

For covering patents, see www.legrand.us/patents.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of de-rating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Specifications

General Info

Color	Brown	UPC Number	785007301885
-------	-------	------------	--------------

Country Of Origin	China	Product Line	Pass & Seymour
-------------------	-------	--------------	----------------

Application Sector	Commercial	Type	Dimmer
--------------------	------------	------	--------

Standard	cULus, California Title 24 Compliant
----------	--------------------------------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	95219
--------------	-----	---------------------	-------

Technical Information

Number of Poles	Single Pole	Voltage	120 V
-----------------	-------------	---------	-------

Frequency Rating	60 Hz	Load	Up to rating of device (including de-rating)
------------------	-------	------	--

Environmental Conditions	Non-Condensing Humidity: Less than 95	Operating Cycles	100
--------------------------	---------------------------------------	------------------	-----