



Ganging conventional dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change all that. Unlike the others, Titan Dimmers are a complete solution that saves time and money and offers end-users a superior, more convenient, better-looking multi-gang installation.

Features & Benefits

For use with 2 wire 120V and 277V fluorescent dimming ballasts	Field configurable wall plate system
Labeling system	Adjustable low end output voltage
Shipped with protective film	Rugged construction
Superior ratings with a minimum of derating when ganged	Simple to plan the rough-in
Available in single pole slide-to-OFF and single pole/3-way preset models	Attractive European styling. Eye-catching packaging
Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system	Blank center plate included

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
------------------	-----	------------------	-------

Amperage	1100 A	Number of Poles	Single Pole
Voltage	120.0 V	Load	Up to rating of device (including de-rating)
Environmental Conditions	Non-Condensing Humidity: Less than 95%		