



Pass and Seymour
Discontinued - Titan Series Magnetic Low-Voltage Dimmer, Red
Part No. CDLV1103PRED



Slide Dimmer, Low Voltage, Single Pole/3Way PRESET 1100VA,
Black

Features & Benefits

Field configurable wall plate system.

Adjustable low end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system.

For covering patents, see www.legrand.us/patents.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of de-rating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	China	Application Sector	Commercial
Standard	RoHS, cULus, UL Listed	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Amperage	1100 A	Wattage	1100 W
Voltage	120.0 V	Load	Low Voltage
Environmental Conditions	Humidity: Less than 95% non condensing		